

BOSUN CHAIRS

- WITH PROOF LOAD TEST CERTIFICATE



**STAMPED WITH SWL - 136KG MAX
MILD STEEL GALVANISED SUPPORT FRAME
GLASS REINFORCED PLASTIC SEAT TUB**

**SEAT TUB: 600MM WIDE X 405MM LONG X 300MM DEEP
700MM OVERALL HEIGHT**

44MM INNER DIAMETER CURLED AND WELDED EYE LOOP

IMPORTANT SAFETY CONSIDERATIONS

Usage: A bosun's chair is a work seat, classified as lifting equipment. **It is not a fall arrest system or device.** You are legally required to use it in conjunction with an independent fall arrest system, typically involving a full-body harness and a separate anchor point.

Inspection: A bosun's chair must be maintained in a safe condition and are subject to mandatory, thorough inspections by a 'competent person' at least every six months. Always check for cracks, stress fractures, or degradation in the fiberglass seat before use. If the seat is damaged, it must be removed from service immediately and replaced.

Always adhere to the specific safe working load capacity (136KG) and usage guidelines provided. Do not modify the chair or its rigging, as this invalidates its safety certification.

Please refer to LOLER (Lifting Operations and Lifting Equipment Regulations 1998) for more information.